



# DISINFECTING EQUIPMENT



Prevail™ is a member of the Virox family of brands.

Prevail® Disinfectants, powered by Accelerated Hydrogen Peroxide®, is approved by Health Canada as an effective disinfectant to fight against ASFv and other deadly pathogens. Its gentle formulation is non-toxic and safe to protect your livelihood with the utmost care in mind.



# DISINFECTING EQUIPMENT

This line of equipment is approved for use with Accelerated Hydrogen Peroxide® disinfectants such as Prevail™ Concentrate Disinfectant.

Each piece of equipment, when properly calibrated, allows for accurate dilution of chemical concentrate to the desired ratio.

## FOAMERS

### MODEL 20 SS COMBO AIRLESS FOAMER/SPRAYER

#### Overview

This unit is an airless foam and spray applicator featuring a quick connect chemical injector that attaches to a pressure washer outlet. This venturi unit draws and blends chemical concentrate into the water stream to create an accurately diluted solution. The solution then flows through the hose and gun to the airless foam wand which injects atmospheric air to create and project wet, clinging foam onto surfaces up close or at distances up to 25 feet with interchangeable fan and zero degree nozzles. Quick connect the fan pattern sprayer nozzle to apply non-foaming chemicals.

#### Key Features

- Quick connect the airless foam wand to project wet, clinging foam
- Foam increases chemical contact time and effectiveness, and provides visual confirmation of coverage
- Foam impacts at a lower pressure than spray, allowing a pressure washer to be used on more delicate surfaces
- Use the fan pattern foam nozzle for wide coverage or the zero degree foam nozzle for increased range (up to 25")
- Quick connect the fan pattern sprayer nozzle to apply a chemical spray
- Industrial-strength, all stainless steel design ensures durability and reliable performance
- Designed for use with 3.5–5.5 GPM pressure washers
- Draws chemical out of any sized container and accurately dilutes to the required ratio
- Chemical injector at the pressure washer output eliminates the need to carry chemicals

#### Includes

- 3/8" quick connect machined stainless steel injector body
- 6' chemical suction tube and strainer
- 20 color-coded precision metering tips to set dilution ratios


#### Recommended



Water pressure varies widely. AHP1750 Test Strips are highly recommended to set up and to periodically confirm desired dilutions.

### Model 20 SS Combo Airless Foamer/Sprayer

Part Number: CD001





# HOSE-END FOAMERS

## MODEL 25 COMPACT AIRLESS FOAMER

### Overview

A durable hose-end foamer for both diluting and applying Prevail onto any surface. This unit uses facility's water pressure to pull the concentrate and blend it into the water stream, which then flows through the wand to create a clinging, wet foam.

### Key Features

- Attaches to standard garden hose or 1/2" water connections
- Creates rich, wet foam which increases chemical cling time and surface coverage
- Foam provides visual verification that all areas are covered
- Projects foam up to 12' (depending on water pressure)
- The stainless-steel quick connect adapter features a 6-ball socket for secure assembly
- Light, 32 oz HDPE bottle reduces wrist and arm fatigue and the risk of repetitive strain injuries
- Great performance with pressure as low as 20 PSI
- Impact resistant lid stands up to substantial abuse

### Foamer Includes

- Machined polypropylene foamer body
- Quick connect adapter SS
- 32 oz wide-mouth, HDPE bottle
- Heavy-duty bottle lid
- 20 color-coded metering tips
- Garden hose gun with inlet screen/filter

### Recommended



Water pressure varies widely. AHP1750 Test Strips are highly recommended to set up and to periodically confirm desired dilutions.

Model 25 Compact  
Airless Foamer

Part Number: CD013



#### DISCLAIMER

You must read and follow the instructions on the label for our product and use the product for the particular applications specified on the product label. To the full extent permitted under applicable law, Virox Technologies Inc. shall not be liable for any damages whatsoever, arising out of or otherwise in connection with any failure to follow those instructions or any use of its products which is not specified on the product's label. The instructions on the product label are not a warranty, express or implied, and Virox Technologies, Inc. expressly disclaims any implied warranties, including any warranty of fitness for a particular purpose. Under applicable law, some of the above waivers or disclaimers of warranty, or exclusions of liability for certain types of damages may not apply to you. In such cases, our liability will be limited to the fullest extent permitted by applicable law.



Contact [ethoguard.com](http://ethoguard.com) to order.

# ACCESSORIES

## Disinfecting Accessories

Our disinfecting accessories make chemical management simpler, neater, cleaner, and safer.

Each accessory is suggested for use with Accelerated Hydrogen Peroxide® disinfectants such as Prevail™ Concentrate and Prevail™ Ready to Use Disinfectants.

These convenient accessories complement our wide range of disinfecting equipment.



### 3.78L Pump

**Part Number: CD003**

An approved pump for the Prevail 3.78L bottle to dispense the concentrate solution into a measuring cup.



### 18.9L Pump

**Part Number: CD004**

An approved pump for the Prevail 18.9L pail to dispense the concentrate solution into a measuring cup.



### 200L Pump

**Part Number CD005**

An approved pump for the Prevail 200L drum to dispense the concentrate solution into a measuring cup. This pump dispenses 14oz of solution per stroke.



### 1L Trigger Sprayer/Foamer

**Part Number: CD006**

Applies Prevail Ready to Use or diluted concentrate solutions in a foam or aerosolized solution. Foaming is an alternative to an aerosolized spray which results in visible surface coverage and slower evaporation.



### 1L Empty Bottle

**Part Number: CD007**

Empty bottle to dispense Ready to Use or diluted concentrate and prepare for application.



### AHP1750 Test Strips

**Part Number: 1750**

AHP1750 test strips are used to test and confirm the dilutions. These strips are easy-to-use dip-and-read strips and will confirm the 1:40 and 1:128 dilutions. (50 test strips)



### Workplace Labels (Secondary Product Labels)

**Concentrate Part Number: CD019**  
**Ready to Use, Part Number: CD029**

Workplace labels are designed for secondary bottles containing diluted Prevail Concentrate solution or dispensing Prevail Ready to Use. Labels are used to identify the expiry date, lot number and dilution rate for diluted concentrates.

### Metering Tips

**Part Number: 909-HDP009**

For use with compact airless foamers and mixing stations to ensure accurate dilutions based on facility water pressure.



# PREvail®

## FARM DISINFECTANTS



### Ideal for disinfection and cleaning of:

- Agricultural farms and barns
- Transportation vehicles

### CONCENTRATE

#### 5 min contact time

Prevail™ Concentrate is ideal for large surfaces, providing a cost effective option for daily use.

- Easy to dilute and apply: use a 1:40 dilution (25 mL/L) for disinfection
- Long shelf life of 30 days once diluted

### WIPES

#### 1 min contact time

Prevail™ Wipes provides an easy, convenient and effective way to disinfect your smaller surfaces (e.g., inside of truck cabs, handheld equipment, steering wheels, and other high-touch surfaces).

### READY-TO-USE

#### 1 min contact time

Prevail™ Ready-to-Use is a unique pre-mixed solution that requires no dilution. Ideal for daily use and on smaller surfaces (e.g., truck cabs, boot baths, cages, and counters).

[www.PrevailFarm.ca](http://www.PrevailFarm.ca)

### Prevail is effective against\*:

- African Swine Fever Virus (ASFv)
- Porcine Epidemic Diarrhea Virus (PEDv)
- Avian Influenza Virus
- Porcine Reproductive & Respiratory Syndrome Virus (PRRSv)

\*Refer to reference sheets for a complete list of efficacy claims and use directions



#### POWERFUL

Proven efficacy against a broad spectrum of organisms in just 1-5 minutes. At least 2x faster than the competition.



#### SAFER

No harsh chemical smell and is non-irritating to eyes and skin when used as directed.



#### CLEANER

Formulated with powerful detergents to provide exceptional cleaning capabilities. Prevail's excellent foaming ability allows you to easily visualize surface coverage, saving time and money.



#### SUSTAINABLE

Biodegradable formulations - the active ingredient breaks down to water and oxygen for easy disposal and minimal environmental impact.



#### COMPATIBLE

Designed to be compatible with a wide range of materials, protecting assets by reducing corrosion and wear.

To Purchase Contact:



**EthoGuard**  
Your Biosecurity Partner

[www.ethoguard.com](http://www.ethoguard.com)  
[info@ethoguard.com](mailto:info@ethoguard.com)  
tel: 226-523-5969

Contact [ethoguard.com](http://ethoguard.com) to order.



Contact [ethoguard.com](http://ethoguard.com) to order.